



KDN280A

## Insulated busbar 2P 80A fork 16mm<sup>2</sup> 12M

### Technical properties

#### Architecture

Number of poles	2 P
Type of pole	2 P

#### Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

#### Voltage

Max operating voltage	400 V
-----------------------	-------

#### Electric current

Rated current	80 A
---------------	------

#### Dimensions

Length	210 mm
Pitch	17.8 mm

#### Materials

Colour	stone grey
--------	------------

#### Installation, mounting

Suitable to a device with an auxiliary	No
--	----

#### Connection

Connection cross-sect. rigid cable	16mm <sup>2</sup>
Suitable for product with neutral busbar	Yes

#### Equipment

Number of appliances to build in	6
----------------------------------	---

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Insulated	Yes
-----------	-----