



KDN280A

Insulated busbar 2P 80A fork 16mm² 12M

Technical properties

Architecture

Number of poles	2 P
-----------------	-----

Main electrical features

Rated operational voltage U _e	230 / 400 V
--	-------------

Voltage

Max operating voltage	400 V
-----------------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Length	210 mm
--------	--------

Pitch	17.8 mm
-------	---------

Materials

Colour	stone grey
--------	------------

Installation, mounting

Suitable to a device with an auxiliary	No
--	----

Connection

Connection cross-sect. rigid cable	16mm ²
------------------------------------	-------------------

Suitable for product with neutral busbar	Yes
--	-----

Connector type	busbar fork
----------------	-------------

Equipment

Number of appliances to build in	6
----------------------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Use conditions

Insulated	Yes
-----------	-----