



KDN380A

### Insulated busbar 3P 80A fork 16mm<sup>2</sup> 12M

#### Technical properties

##### Electric current

Rated current	80 A
---------------	------

##### Architecture

Number of poles	3
-----------------	---

##### Dimensions

Length	210 mm
--------	--------

##### Voltage

Rated impulse withstand voltage U <sub>imp</sub>	4500 V
--	--------

##### Connection

Cross-section rigid conductor	16 mm <sup>2</sup>
-------------------------------	--------------------

Connector/plug type	Phase busbar with fork
---------------------	------------------------

##### Capacity

Number of modules	12
-------------------	----