



KF81A

## Cable terminal 1P prong 1 cable 25mm<sup>2</sup>

### Technical properties

#### Architecture

Number of poles	1 P
-----------------	-----

#### Functions

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

#### Electric current

Rated current	80 A
---------------	------

#### Connection

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
Connection cross-sect. rigid cable	25mm <sup>2</sup>
Terminal cross-section	25 mm <sup>2</sup>

#### Accessories included

Type of accessory	Connection clamp
-------------------	------------------

#### Equipment

Number of outputs	0
Number of inputs	1

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes