



KF84A

**Cable terminal 1P fork 1 cable 25mm<sup>2</sup>**

**Technical properties**

**Architecture**

Number of poles	1 P
-----------------	-----

**Functions**

Suitable for fine strand conductors	No
Suitable for fine strand conductors without cable end sleeve	No
Suitable for extra fine-strand conductors	No
Suitable for extra fine-strand conductors without cable end sleeve	No

**Electric current**

Rated current	80 A
---------------	------

**Connection**

Connection cross-sect. flexible conductor	16mm <sup>2</sup>
Connection cross-sect. rigid cable	25mm <sup>2</sup>
Terminal cross-section	25 mm <sup>2</sup>

**Accessories included**

Type of accessory	Connection clamp
-------------------	------------------

**Equipment**

Number of outputs	0
Number of inputs	1

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	Yes