



KN10N

**Terminal, QuickConnect, neutral, 10 connections**

**Technical properties**

**Architecture**

Number of poles	1 P
Type of pole	1 P

**Functions**

Suitable for flexible core	Yes
----------------------------	-----

**Main electrical features**

Nominal voltage	230 V
-----------------	-------

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth of installed product	34 mm
Height of installed product	33 mm
Width of installed product	45 mm

**Materials**

Copper weight of the product	0.011 kg
------------------------------	----------

**Connection**

Conductor cross-section (flexible), with wire end sleeve	1.5...25 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...25 mm <sup>2</sup>

**Settings**

terminal type	N terminal
---------------	------------

**Safety**

REACH conform	No
RoHS conform	Yes
Halogen free	No