



LF1501509001

PI-36
 (A)

Trunking from PVC LF 15x15mm cream white

Technical properties

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	15 mm
Length	2000 mm
Trunking width	15 mm
Distance bottom-punch along trunking-direction	125 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	1
Maximum number of cables (Ø 11 mm, 50% fill)	1

Cover, door

Lid shape	premounted
-----------	------------

Materials

Colour	cream white
RAL colour	RAL 9001 - Cream
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Cable

Internal/useful cross section	150 mm ²
-------------------------------	---------------------

Equipment

Number of fix dividers	0
Number of plugable separators	0
Compartment quantity	1
Cable retainers per meter	0

Standards

European directive RoHs	voluntary compliance
-------------------------	----------------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------