



LF2502507030



Trunking from PVC LF 25x25mm stone grey

Technical properties

Architecture

Fixing mode bottom punched

Configuration

Antibacterial treatment No

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 25 mm

Length 2000 mm

Trunking width 25 mm

Distance bottom-punch along trunking-direction 125 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 2

Maximum number of cables (Ø 11 mm, 50% fill) 2

Cover, door

Lid shape loose

Materials

Colour stone grey

RAL colour RAL 7030 - Stone grey

Material PVC

Material group plastic

Type of surface treatment untreated

Transparent No

Cable

Internal/useful cross section 500 mm²

Equipment

Compartment quantity 1

Standards

Approvals EN50085-2-1

European directive RoHs voluntary compliance

Safety

Protection index IP	IP30
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------
