



LF4004009001



## Trunking from PVC LF 40x40mm cream white

### Technical properties

#### Connectivity

|                   |                            |
|-------------------|----------------------------|
| Trunking coupling | Pre-equipped with couplers |
|-------------------|----------------------------|

#### Dimensions

|                                                |         |
|------------------------------------------------|---------|
| Trunking height                                | 40 mm   |
| Length                                         | 2000 mm |
| Trunking width                                 | 40 mm   |
| Distance bottom-punch along trunking-direction | 125 mm  |

#### Capacity

|                                              |   |
|----------------------------------------------|---|
| Maximum number of cables (Ø 11 mm, 50% fill) | 6 |
| Maximum number of cables (Ø 11 mm, 50% fill) | 6 |

#### Cover, door

|           |       |
|-----------|-------|
| Lid shape | loose |
|-----------|-------|

#### Materials

|                           |                  |
|---------------------------|------------------|
| Colour                    | cream white      |
| RAL colour                | RAL 9001 - Cream |
| Material                  | PVC              |
| Material group            | plastic          |
| Type of surface treatment | untreated        |
| Transparent               | No               |

#### Cable

|                               |                     |
|-------------------------------|---------------------|
| Internal/useful cross section | 900 mm <sup>2</sup> |
|-------------------------------|---------------------|

#### Equipment

|                               |   |
|-------------------------------|---|
| Number of fix dividers        | 0 |
| Number of plugable separators | 0 |
| Compartment quantity          | 1 |
| Cable retainers per meter     | 0 |

#### Standards

|                         |                      |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

#### temperatur

|                     |            |
|---------------------|------------|
| Ambient temperature | -5...65 °C |
|---------------------|------------|