


LFR2002009010T2



Mini flexible trunking on roll with adhesive tape LFR 20x20mm PVC in pure white

Technical properties

Dimensions

Height	20 mm
Width	20 mm
Length	20000 mm
Inner cross-section	342 - 342 mm ²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	2
--	---

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9010
Colour	Pure white

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Trunking coupling	Without coupling
-------------------	------------------

Equipment

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	0
Cable retaining clip included	No
With protective film	No