



LNH0050M

## HRC LV fuse NH000 gG AC500V 50A double indicator with live gripping-lugs

### Technical properties

#### Architecture

Curve	gG
-------	----

#### Fuse

Fuse size	NH000
Fuse characteristics	gG

#### Voltage

Type voltage supply	AC/DC
---------------------	-------

#### Electric current

Rated current	50 A
---------------	------

#### Use conditions

Insulated	No
-----------	----

#### Main electrical attributes

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	120 kA
---	--------

#### Power

Total power loss under I <sub>N</sub>	4,10 W
---------------------------------------	--------

#### Dimensions

Height	58,50 mm
Width	21 mm
Depth	79 mm