



LNH0063M

**HRC LV fuse NH000 gG AC500V 63A double indicator with live gripping-lugs**

**Technical properties**

**Architecture**

Curve gG

**Main electrical features**

Rated short circuit breaking capacity  $I_{cn}$  AC according IEC60898-1 120 kA

Rated operational voltage  $U_e$  500 V

Type of supply voltage AC/DC

**Voltage**

Rated voltage DC 250 V

**Electric current**

Cut off current 120 kA

Rated current 63 A

**Fuse**

CharactFuse gG

Fuse Size NH000

**Dimensions**

Depth of installed product 79 mm

Height of installed product 58.5 mm

Width of installed product 21 mm

**Power**

Total power loss under  $I_N$  5.4 W

**Standards**

Approvals VDE, EAC

**Safety**

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Altitude 2000 m

Insulated No

**Identification**

Device family LNH