



LNH0080M

**HRC LV fuse NH000 gG AC500V 80A double indicator with live gripping-lugs**

**Technical properties**

**Architecture**

Curve gG

**Fuse**

Fuse size NH000

Fuse characteristics gG

**Voltage**

Type voltage supply AC/DC

**Electric current**

Rated current 80 A

**Use conditions**

Insulated No

**Main electrical attributes**

Rated short-circuit breaking capacity  $I_{cn}$  AC according to IEC 60898-1 120 kA

**Power**

Total power loss under  $I_N$  6,50 W

**Dimensions**

Height 58,50 mm

Width 21 mm

Depth 79 mm