



LNH0080M

HRC LV fuse NH000 gG AC500V 80A double indicator with live gripping-lugs

Technical properties

Architecture

Curve gG

Fuse

Fuse size NH000

Fuse characteristics gG

Voltage

Type voltage supply AC/DC

Electric current

Rated current 80 A

Use conditions

Insulated No

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1 120 kA

Power

Total power loss under I_N 6,50 W

Dimensions

Height 58,50 mm

Width 21 mm

Depth 79 mm