



LNH0100M

HRC LV fuse NH000 gG AC500V 100A double indicator with live gripping-lugs

Technical properties

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
--	--------

Rated operational voltage U_e	500 V
---------------------------------	-------

Voltage

Rated voltage DC	250 V
------------------	-------

Electric current

Cut off current	120 kA
-----------------	--------

Rated current	100 A
---------------	-------

Fuse

Fuse Size	NH000
-----------	-------

Dimensions

Depth of installed product	79 mm
----------------------------	-------

Height of installed product	58.5 mm
-----------------------------	---------

Width of installed product	21 mm
----------------------------	-------

Power

Total power loss under I_N	7.5 W
------------------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Altitude	2000 m
----------	--------

Insulated	No
-----------	----