



LNH0100M

HRC LV fuse NH000 gG AC500V 100A double indicator with live gripping-lugs

Technical properties

Architecture

Curve	gG
-------	----

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
Rated operational voltage U_e	500 V
Type of supply voltage	AC/DC

Voltage

Rated voltage DC	250 V
------------------	-------

Electric current

Cut off current	120 kA
Rated current	100 A

Fuse

CharactFuse	gG
Fuse Size	NH000

Dimensions

Depth of installed product	79 mm
Height of installed product	58.5 mm
Width of installed product	21 mm

Power

Total power loss under I_N	7.5 W
------------------------------	-------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Altitude	2000 m
Insulated	No