



LNH0125M

**HRC LV fuse NH00 gG AC500V 125A double indicator with live gripping-lugs**

**Technical properties**

**Main electrical features**

Rated short circuit breaking capacity I <sub>cn</sub> AC according IEC60898-1	120 kA
---	--------

Rated operational voltage U <sub>e</sub>	500 V
--	-------

**Voltage**

Rated voltage DC	250 V
------------------	-------

**Electric current**

Cut off current	120 kA
-----------------	--------

Rated current	125 A
---------------	-------

**Fuse**

Fuse Size	NH00
-----------	------

**Dimensions**

Depth of installed product	79 mm
----------------------------	-------

Height of installed product	58.5 mm
-----------------------------	---------

Width of installed product	21 mm
----------------------------	-------

**Power**

Total power loss under I <sub>N</sub>	10 W
---------------------------------------	------

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Use conditions**

Altitude	2000 m
----------	--------

Insulated	No
-----------	----