



LNH0160M

## NH fuse NH00 gG 500V 160A central indicator live grippings

### Technical properties

#### Architecture

Curve	gG
-------	----

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
--	--------

Rated operational voltage $U_e$	500 V
---------------------------------	-------

Type of supply voltage	AC/DC
------------------------	-------

#### Voltage

Rated voltage DC	250 V
------------------	-------

#### Electric current

Cut off current	120 kA
-----------------	--------

Rated current	160 A
---------------	-------

#### Fuse

CharactFuse	gG
-------------	----

Fuse Size	NH00
-----------	------

#### Dimensions

Depth of installed product	51 mm
----------------------------	-------

Height of installed product	79 mm
-----------------------------	-------

Length	51 mm
--------	-------

Width of installed product	21 mm
----------------------------	-------

#### Power

Total power loss under $I_N$	12 W
------------------------------	------

#### Standards

Approvals	VDE, EAC
-----------	----------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

#### Use conditions

Altitude	2000 m
----------	--------

Insulated	No
-----------	----

#### Identification

