



LNH1160M

HRC LV fuse NH1 gG AC500V 160A double indicator with live gripping-lugs

Technical properties

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
--	--------

Rated operational voltage U_e	500 V
---------------------------------	-------

Voltage

Rated voltage DC	250 V
------------------	-------

Electric current

Cut off current	120 kA
-----------------	--------

Rated current	160 A
---------------	-------

Fuse

Fuse Size	NH1
-----------	-----

Dimensions

Depth of installed product	135 mm
----------------------------	--------

Height of installed product	64.5 mm
-----------------------------	---------

Width of installed product	135 mm
----------------------------	--------

Power

Total power loss under I_N	14.6 W
------------------------------	--------

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Altitude	2000 m
----------	--------

Insulated	No
-----------	----