



LNH1160M

HRC LV fuse NH1 gG AC500V 160A double indicator with live gripping-lugs

Technical properties

Architecture

Curve gG

Fuse

Fuse size NH1

Fuse characteristics gG

Voltage

Type voltage supply AC/DC

Electric current

Rated current 160 A

Use conditions

Insulated No

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1 120 kA

Power

Total power loss under I_N 14,60 W

Dimensions

Height 64,50 mm

Width 135 mm

Depth 135 mm