



LNH2200M

HRC LV fuse NH2C gG AC500V 200A double indicator with live gripping-lugs

Technical properties

Architecture

Curve gG

Fuse

Fuse size NH2C

Fuse characteristics gG

Voltage

Type voltage supply AC/DC

Electric current

Rated current 200 A

Use conditions

Insulated No

Main electrical attributes

Rated short-circuit breaking capacity I_{cn} AC according to IEC 60898-1 120 kA

Power

Total power loss under I_N 18,50 W

Dimensions

Height 150 mm

Width 39 mm

Depth 72,5 mm