



LNH2200M

NH fuse NH2C gG 500V 200A central indicator live gripping lugs

Technical properties

Main electrical features

Rated short circuit breaking capacity I_{cn} AC according IEC60898-1	120 kA
Rated operational voltage U_e	500 V
Type of supply voltage	AC

Electric current

Cut off current	120 kA
Rated current	200 A

Dimensions

Depth of installed product	150 mm
Height of installed product	72.5 mm
Length	62 mm
Width of installed product	49 mm

Power

Total power loss under I_N	18.5 W
------------------------------	--------

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Altitude	2000 m
Insulated	No