



LNH2200M

**HRC LV fuse NH2C gG AC500V 200A double indicator with live gripping-lugs**

**Technical properties**

**Architecture**

Curve	gG
-------	----

**Main electrical features**

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	120 kA
Rated operational voltage $U_e$	500 V
Type of supply voltage	AC/DC

**Voltage**

Rated voltage DC	250 V
------------------	-------

**Electric current**

Cut off current	120 kA
Rated current	200 A

**Fuse**

CharactFuse	gG
Fuse Size	NH2C

**Dimensions**

Depth of installed product	150 mm
Height of installed product	72.5 mm
Width of installed product	49 mm

**Power**

Total power loss under $I_N$	18.5 W
------------------------------	--------

**Standards**

Approvals	VDE, EAC
-----------	----------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Use conditions**

Altitude	2000 m
Insulated	No

**Identification**

Device family	LNH
---------------	-----