



LT150

**Fuse switch disconnecter LT size 1 250A for mounting plate, terminal M10**

**Technical properties**

**Electric current**

Rated current	250 A
Rated short-time withstand current I <sub>cw</sub> 1s IEC 60947	8,60 kA
Acceptable current rating AC22 category B	250 A

**Fuse**

Fuse size	NH1
-----------	-----

**Connection**

Cross-section flexible conductor	6 - 150 mm <sup>2</sup>
Cross-section rigid conductor	6 - 150 mm <sup>2</sup>

**Use conditions**

Operating temperature	-25 - 55 °C
-----------------------	-------------

**Installation, mounting**

Nominal tightening torque	20 - 20 Nm
Mounting on	Mounting plate

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Total power loss under I <sub>N</sub>	18 W
---------------------------------------	------

**Endurance**

Number of mechanical operations	1400
Electric endurance in number of cycles	200
Total service life (mechanical and electrical endurance) IEC 60947-3 Table 4	1600

**Voltage**

Rated insulation voltage U <sub>i</sub>	1000 V
Rated impulse withstand voltage U <sub>imp</sub>	8000 V

**Safety**

Ingress Protection (IP) class	IP3X
-------------------------------	------

**Dimensions**

Height	304 mm
Width	184 mm

