



M5690



**Flexible slotted panel trunking Polyamid halogenfree 10mm Länge=0,25m light grey**

**Technical properties**

**Architecture**

Flexible Yes

**Configuration**

Side wall configuration Slotted

**Electric current**

Current leak stable Yes

**Dimensions**

Trunking height 10 mm

Length 250 mm

Trunking width 10 mm

Slot width 8 mm

Tongue width 4.5 mm

**Cover, door**

Lid shape none

**Materials**

Material group plastic

Type of surface treatment untreated

**Installation, mounting**

Base punching With base punching

Fixing type bottom punching

**Cable**

Number of wires 1,5 mm<sup>2</sup> - 40% filling degree 8

Internal/useful cross section 100 mm<sup>2</sup>

Number of wires 2,5 mm<sup>2</sup> - 40% filling degree 5

Number of wires 1,0 mm<sup>2</sup> - 40% filling degree 10

**Standards**

European directive RoHs voluntary compliance

UL 94 classification V0

**Safety**

REACH conform Yes

RoHS conform	Yes
Halogen free	Yes
<b>temperatur</b>	
Ambient temperature	-25...90 °C