

1.5 - 10 mm²

1 - 6 mm²



SK601

Reverser 20 2F

Technical properties

Architecture	
Number of poles	2
Type of pole	2P
Electric current	
Rated current	20 A
Rated conditional short-circuit current lcc with gl-gG fuses	8 kA
Voltage	
Rated operational voltage Ue	400 - 400 V
Type voltage supply	AC
Rated insulation voltage Ui	690 V
Capacity	
Number of modules	3
Safety	
Ingress Protection (IP) class	IP20
Frequency	
Frequency	50 - 50 Hz
Dimensions	
Height	85 mm
Width	53 mm
Depth	64 mm
Equipment	
Number of NO contacts	2
Number of NC contacts	2
Use conditions	
Operating temperature	-10 - 40 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section flexible conductor

Cross-section rigid conductor