




SK603



## Ammeter switch 3 O

### Technical properties

#### Configuration

Number of modules	3
-------------------	---

#### Controls and indicators

Number of positions of the switch	4
-----------------------------------	---

#### Main electrical features

Frequency	50 Hz
-----------	-------

#### Voltage

Rated insulation voltage	690 V
--------------------------	-------

#### Electric current

Rated current	20 A
---------------	------

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

#### Power

Total power loss under IN	1 W
---------------------------	-----

#### Network configuration

Network type	tree-phase with neutral
--------------	-------------------------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------