



SK604



## Changeover switch 4DIRo

### Technical properties

#### Configuration

Number of modules	3
-------------------	---

#### Controls and indicators

Number of positions of the switch	5
-----------------------------------	---

#### Main electrical features

Frequency	50 Hz
-----------	-------

#### Voltage

Rated insulation voltage	690 V
--------------------------	-------

#### Electric current

Rated current	20 A
---------------	------

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	70 mm
----------------------------	-------

#### Power

Total power loss under IN	1 W
---------------------------	-----

#### Connection

Connection cross-sect. flexible conductor	1,5 / 10mm <sup>2</sup>
---	-------------------------

Connection cross-sect. rigid cable	1 / 6mm <sup>2</sup>
------------------------------------	----------------------

Type of connection	with screw
--------------------	------------

#### Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

#### Use conditions

Operating temperature	-10...40 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------