




SK604



Changeover switch 4DIRo

Technical properties

Electric current

Rated current 20 A

Capacity

Number of modules 3

Frequency

Frequency 50 - 50 Hz

Use conditions

Operating temperature -10 - 40 °C

Storage/transport temperature -40 - 80 °C

Connectivity

Type of connection Screw terminal

Connection

Cross-section flexible conductor 1.5 - 10 mm²

Cross-section rigid conductor 1 - 6 mm²

Power

Total power loss under IN 1 W

Dimensions

Height 85 mm

Width 70 mm

Depth 64 mm

Safety

Ingress Protection (IP) class IP20

Voltage

Rated insulation voltage Ui 690 V

Rated operational voltage Ue 660 - 660 V

Equipment

With battery No