



SL1807507030



**Trunking 18x75, grey**

**Technical properties**

**Configuration**

Antibacterial treatment	No
Self-adhesive	No

**Dimensions**

Trunking height	18 mm
Length	2000 mm
Trunking width	73 mm
Width of installed product	73 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill)	4
Maximum number of cables (Ø 11 mm, 50% fill)	4

**Cover, door**

Lid with softlip	No
------------------	----

**Materials**

Material group	plastic
Type of surface treatment	untreated

**Equipment**

Number of fix dividers	3
Compartment quantity	4
Number of channels	4

**Standards**

European directive RoHS	voluntary compliance
-------------------------	----------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK08

**temperatur**

Ambient temperature	-5...65 °C
---------------------	------------