



SL1807507030



Trunking 18x75, grey

Technical properties

Configuration

Antibacterial treatment	No
Self-adhesive	No

Dimensions

Trunking height	18 mm
Length	2000 mm
Trunking width	73 mm
Width of installed product	73 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	4
Maximum number of cables (Ø 11 mm, 50% fill)	4

Cover, door

Lid with softlip	No
------------------	----

Materials

Colour	stone grey
Material group	plastic
Type of surface treatment	untreated

Equipment

Number of fix dividers	3
Compartment quantity	4
Number of channels	4

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Protection index IP	IP30
---------------------	------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------