



SM005

## Analogue ammeter 0-5A direct reading

### Technical properties

#### Capacity

Number of modules	4
-------------------	---

#### Use conditions

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 80 °C

#### Connection

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

#### Dimensions

Height	85 mm
Width	70 mm
Depth	54 mm

#### Measurement

Current measurement range	0 - 5 A
Type of measuring instrument	Analog

#### Power

Power consumption VA	1,10 VA
Total power loss under IN	1,10 W

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Installation, mounting

Mounting on	DIN rail
-------------	----------

#### Functions

Accuracy class	0.015
----------------	-------

#### Voltage

Rated insulation voltage Ui	2000 V
-----------------------------	--------

#### Frequency

Frequency	45 - 65 Hz
-----------	------------