



SM005

## Analogue ammeter 0-5A direct reading

### Technical properties

#### Functions

Precision class	1.5%
-----------------	------

#### Configuration

Number of modules	4
-------------------	---

#### Controls and indicators

Measurement scale	5 A
-------------------	-----

#### Main electrical features

Frequency	45/65 Hz
-----------	----------

#### Voltage

Rated insulation voltage	2000 V
--------------------------	--------

#### Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

#### Power

Power consumed	1.1 VA
Total power loss under IN	1.1 W

#### Installation, mounting

Modular version	Yes
-----------------	-----

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>

#### Safety

REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-25...50 °C
Storage/transport temperature	-40...80 °C