



SM101C

Communicant Modular multifunction meter

Technical properties

Functions

Precision class	0.5%
-----------------	------

Configuration

Number of modules	4
-------------------	---

Main electrical features

Rated operational voltage Ue	200 / 230 / 277 V
------------------------------	-------------------

Dimensions

Depth of installed product	50 mm
Height of installed product	45 mm
Length	67 mm
Width of installed product	73 mm

Power

Power consumed	5 VA
Total power loss under IN	5 W

Measurement

Frequency measuring range	45 to 65 Hz
Voltage measurement range	50 to 500 V
Type of measuring instrument	multimeter

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	0,5 / 4mm ²
Connection cross-sect. rigid cable	0,5 / 4mm ²

Equipment

Type of display	Digital
Digits number	4

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature

-10...55 °C

Storage/transport temperature

-20...70 °C