



SM150

## Analogue ammeter 0-150A indirect reading

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Configuration

Number of modules	4
-------------------	---

#### Controls and indicators

Measurement scale	150 A
-------------------	-------

#### Voltage

Rated insulation voltage	2000 V
--------------------------	--------

#### Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

#### Power

Power consumed	1.1 VA
Total power loss under IN	1.1 W

#### Installation, mounting

Modular version	Yes
-----------------	-----

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-25...50 °C
Storage/transport temperature	-40...80 °C