



SM600

Analogue ammeter 0-600A indirect reading

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Measurement scale	600 A
-------------------	-------

Voltage

Rated insulation voltage	2000 V
--------------------------	--------

Dimensions

Depth of installed product	54 mm
Height of installed product	85 mm
Width of installed product	70 mm

Power

Power consumed	1.1 VA
Total power loss under IN	1.1 W

Installation, mounting

Modular version	Yes
Mounting type	din-Rail

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-25...50 °C
Storage/transport temperature	-40...80 °C