



SM601

Digital ammeter 0-600A indirect reading

Technical properties

Capacity

Number of modules 4

Use conditions

Operating temperature -10 - 55 °C

Storage/transport temperature -40 - 70 °C

Connection

Cross-section flexible conductor 6 mm²

Cross-section rigid conductor 10 mm²

Dimensions

Height 85 mm

Width 70 mm

Depth 54 mm

Measurement

Current measurement range 0 - 600 A

Type of measuring instrument Digital

Power

Power consumption VA 1 VA

Total power loss under IN 1,10 W

Safety

Ingress Protection (IP) class IP20

Installation, mounting

Mounting on DIN rail

Functions

Accuracy class 0.01

Frequency

Frequency 45 - 65 Hz