



SPB065R

Cartridge L-N Uc 320V In 20kA I_{max} 65kA U_p 1,35kV

Technical properties

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U _e	240 - 415 V
--	-------------

Continuous operating voltage U _c according to IEC 61643-1	305 V
--	-------

Voltage protection level U _p according to IEC 61643-1	1,45 kV
--	---------

Electric current

Nominal discharge current I _n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	20 kA
---	-------

Dimensions

Height	52,4 mm
--------	---------

Width	17,5 mm
-------	---------

Depth	55,3 mm
-------	---------

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN-C, TN-S, TT
--------------	----------------

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------