



SPN015D

## Cartridge 15kA 275V for pluggable SPD

### Technical properties

#### Architecture

Number of poles	1 P
-----------------	-----

#### Configuration

Number of modules	1
-------------------	---

#### Connectivity

Top connection alignment for modular devices	Not applicable
--	----------------

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

Nominal discharge current (In) 8/20 $\mu$ s, IEC 61643)L-N(PEN)/ N-PE	5 kA
---	------

#### Voltage

Maximum continuous operating voltage Uc	275 V
---	-------

Voltage protection level Up according to IEC61643-1	1 kV
---	------

#### Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	15 kA
-------------------------------------	-------

#### Dimensions

Width of installed product	0 mm
----------------------------	------

#### Power

Total power loss under IN	0 W
---------------------------	-----

#### Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------

Altitude	2000 m
----------	--------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------