



SPN015R

Cartridge 15kA 275V for pluggable SPD with reserve

Technical properties

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U_e	230 - 230 V
---------------------------------	-------------

Continuous operating voltage U_c according to IEC 61643-1	275 V
---	-------

Voltage protection level U_p according to IEC 61643-1	1 kV
---	------

Electric current

Nominal discharge current I_n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	5 kA
--	------

Max. discharge (I_{max}) L-N(PEN)/ N-PE	15 kA
---	-------

Dimensions

Height	52,4 mm
--------	---------

Width	17,5 mm
-------	---------

Depth	55,3 mm
-------	---------

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN, TT
--------------	--------

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------