



SPN040D

Cartridge 40kA 275V for pluggable SPD

Technical properties

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U_e	230 - 230 V
---------------------------------	-------------

Continuous operating voltage U_c according to IEC 61643-1	275 V
---	-------

Voltage protection level U_p according to IEC 61643-1	1 kV
---	------

Electric current

Nominal discharge current I_n 8 - 20 μ s L-N(PEN)/N-PE IEC 61643	15 kA
--	-------

Max. discharge (I_{max}) L-N(PEN)/ N-PE	40 kA
---	-------

Dimensions

Height	45 mm
--------	-------

Width	18 mm
-------	-------

Depth	18 mm
-------	-------

Use conditions

Operating temperature	-40 - 55 °C
-----------------------	-------------

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------