



SPN040D

Cartridge 40kA 275V for pluggable SPD

Technical properties

Architecture

Number of poles	1 P
-----------------	-----

Configuration

Number of modules	1
-------------------	---

Connectivity

Top connection alignment for modular devices	Not applicable
--	----------------

Main electrical features

Frequency	50/60 Hz
-----------	----------

Nominal discharge current (I _n) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	15 kA
--	-------

Voltage

Maximum continuous operating voltage U _c	275 V
---	-------

Voltage protection level U _p according to IEC61643-1	1 kV
---	------

Electric current

Max discharge (I _{max}) L-N(PEN)/ N-PE	40 kA
--	-------

Dimensions

Width of installed product	0 mm
----------------------------	------

Power

Total power loss under I _N	0 W
---------------------------------------	-----

Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------

Altitude	2000 m
----------	--------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------