



SPN040R

## Cartridge 40kA 275V for pluggable SPD with reserve

### Technical properties

#### Capacity

Number of modules	1
-------------------	---

#### Voltage

Rated operational voltage $U_e$	230 - 230 V
---------------------------------	-------------

Continuous operating voltage $U_c$ according to IEC 61643-1	275 V
---	-------

Voltage protection level $U_p$ according to IEC 61643-1	1,20 kV
---	---------

#### Electric current

Nominal discharge current $I_n$ 8 - 20 $\mu s$ L-N(PEN)/N-PE IEC 61643	15 kA
--	-------

Max. discharge ( $I_{max}$ ) L-N(PEN)/ N-PE	40 kA
---	-------

#### Dimensions

Height	45 mm
--------	-------

Width	18 mm
-------	-------

Depth	45 mm
-------	-------

#### Use conditions

Operating temperature	-40 - 55 °C
-----------------------	-------------

#### Standards

Requirement class IEC 61643	T2
-----------------------------	----

#### Frequency

Frequency	50 - 60 Hz
-----------	------------