



SPN115R

SPD 1P pluggable 15kA class 2 with reserve + remote contact

Technical properties

Architecture

Type of pole	1 P
--------------	-----

Configuration

Number of modules	1
-------------------	---

Controls and indicators

Indicator lamp	reserve
----------------	---------

Main electrical features

Rated operational voltage Ue	230 / 400 V
------------------------------	-------------

Frequency	50/60 Hz
-----------	----------

Nominal discharge current (In) 8/20 μ s, IEC 61643)L-N(PEN)/ N-PE	5 kA
---	------

Voltage

Maximum continuous operating voltage Uc	275 V
---	-------

Voltage protection level Up according to IEC61643-1	1 kV
---	------

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	15 kA
-------------------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Installation, mounting

Tightening torque	3,6Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	25mm ²
---	-------------------

Connection cross-sect. rigid cable	35mm ²
------------------------------------	-------------------

Standards

Test class IEC61643-11 / VDE0675-6-11	T2
---------------------------------------	----

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Use conditions

Operating temperature	-40...55 °C
-----------------------	-------------

