



SPN140R

SPD 1P pluggable 40kA class 2 with reserve + remote contact

Technical properties

Architecture

Type of pole	1 P
--------------	-----

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Nominal discharge current (In) 8/20μs, IEC 61643)L-N(PEN)/ N-PE	15 kA

Voltage

Maximum continuous operating voltage Uc	275 V
Voltage protection level Up according to IEC61643-1	1.2 kV

Electric current

Max discharge (Imax) L-N(PEN)/ N-PE	40 kA
-------------------------------------	-------

Power

Total power loss under IN	0 W
---------------------------	-----

Standards

Test class IEC61643-11 / VDE0675-6-11	T2
European directive WEEE	concerned

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-40...55 °C
Storage/transport temperature	-40...80 °C