



ST305



Bell transformer 16VA 230V 8-12V

Technical properties

Voltage

Output voltage	8 - 12 V
Rated operational voltage Ue	230 - 230 V
Output voltage 2	12 V
Rated insulation voltage Ui	4000 V

Capacity

Number of modules	3
-------------------	---

Power

Power consumption VA	16 VA
Power	16 VA
Power absorbed	16 W

Dimensions

Height	111 mm
Width	54 mm
Depth	65 mm
Length	64 mm

Safety

Ingress Protection (IP) class	IP20
Temperature protection	Yes

Equipment

Is short-circuit protected	Yes
On/off switch	No

Use conditions

Operating temperature	-20 - 35 °C
-----------------------	-------------

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Intensity output 1	2 A
Intensity output 2	1,33 A

Max. intensity of secondary

2 A

Installation, mounting

Mounting on	DIN rail
-------------	----------

Nominal tightening torque	1,20 - 1,20 Nm
---------------------------	----------------

Internal use only

Number of half modules of 17,5 mm	6
-----------------------------------	---

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----
