



SU215



Buzzer 230V

Technical properties

Electric current

Rated current	0,03 A
---------------	--------

Dimensions

Height	80 mm
Width	18 mm
Depth	65 mm

Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²

Power

Total power loss under IN	6,50 W
Power consumption VA	6,50 VA

Equipment

Noise level	78
-------------	----