



SU215



Buzzer 230V

Technical properties

Architecture

Fixing mode DIN rail type O (symmetrical)

Configuration

Number of modules 1

Main electrical features

Rated operational voltage Ue 230 V

Type of supply voltage AC

Electric current

Operating current 0.03 A

Rated current 0.03 A

Dimensions

Depth of installed product 65 mm

Height of installed product 80 mm

Width of installed product 18 mm

Frequency

Frequency 50 to 0 Hz

Power

Power consumed 6.5 VA

Total power loss under IN 6.5 W

Materials

Material polyamide

Equipment

Noise level 78 dB

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Operating temperature -10...40 °C

Storage/transport temperature -25...60 °C