




TG353

IP44



Big support for KNX weather station

Technical properties

Functions

Precipitation (Yes/No) 1 bit

Controls and indicators

Button / push-button with programming button

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Dimensions (LLxwwxhh) 40x16x6,5

Length, wall bracket 400 mm

Measurement

Measuring range, wind speed 0...35 m/s

Materials

Material aluminium

Material / surface powder-coated

LED control

LED with red programming LED

Installation, mounting

Installation mode for wall and mast assembly

Connection

Bus coupling unit with integral bus coupling unit

Type of connection with plug-in terminals for power supply

Bus connection bus connection via connecting terminal

Scope of delivery

Component with stainless steel screws for fastening

Equipment

Heating with heater element for winter operation

Slewing with an adjustable joint

Use

Differentiation characteristic 3 - Sales with integral bus coupling unit

Safety

Protection index IP	IP44
REACH conform	Yes
RoHS conform	Yes
Use conditions	
Operating temperature	-30...50 °C
temperatur	
Temperature measuring range, linear	-30...80 °C
Identification	
Main design line	KNX
Instructions	
Information text	Ensure correct orientation and free-standing installation.