




TG353

IP44



Big support for KNX weather station

Technical properties

Functions

Precipitation (Yes/No)	1 bit
------------------------	-------

Controls and indicators

Button / push-button	with programming button
----------------------	-------------------------

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Dimensions

Dimensions (LLxwxh)	40x16x6,5
Length, wall bracket	400 mm

Measurement

Measuring range, wind speed	0...35 m/s
-----------------------------	------------

Materials

Material	aluminium
----------	-----------

LED control

LED	with red programming LED
-----	--------------------------

Installation, mounting

Installation mode	for wall and mast assembly
-------------------	----------------------------

Connection

Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

Scope of delivery

Component	with stainless steel screws for fastening
-----------	---

Equipment

Heating	with heater element for winter operation
Slewing	with an adjustable joint

Use

Differentiation characteristic 3 - Sales	with integral bus coupling unit
--	---------------------------------

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions	
Operating temperature	-30...50 °C
temperatur	
Temperature measuring range, linear	-30...80 °C
Identification	
Main design line	KNX
Instructions	
Information text	Ensure correct orientation and free-standing installation.